Thermal cycling test of tin-bismuth and tin plating

ISHIHARA CHEMICAL CO.,LTD. R&D department

Introduction

The tin alloy plating is applied to the IC leadframe in Japan. On the other hand, the pure tin plating is applied to there in the United States and Europe.

We compared the tin whiskers generation of the tin-bismuth finish and the pure tin finish after the thermal cycling test.

Ishihara Chemical co., ltd., all rights reserved

2008/10/6

UNICON ISHIHARA CHEMICAL

Conclusion

Ishihara Chemical R&D report

The long whiskers are generated on the pure tin finish on the alloy42 substrate. On the other hand, the tin-bismuth finish generate no whiskers.

Therefore, it was shown the tin-bismuth finish mitigate the generation of the tin whiskers. In other words, the tin finish doped bismuth can mitigate the tin whiskers.

Table 1 Maximum length of tin whiskers on thermalcycling test

Table 1 Maximum length of the whiskers on thermalcycling test				
Finish	Thermal cycling			
	Substrate	500	1000	1500
Pure tin	CDA194	14	20	26
	alloy42	28	47	67
Tin-bismuth	CDA194	Not obseved	Not obseved	Not obseved
	alloy42	Not obseved	Not obseved	Not obseved

Unit:micrometer



Experimental

Experimental condition

Whisker observation method

- Thermal cycling test: -45deg.C to +80deg.C (20min./cycle)

 Test pieces
- Leadframe: copper alloy(CDA194) and alloy42
- Finish:
 - Pure tin plating process :General pure tin process
 - Tin-2%bismuth plating process :UTB PF-05SH process
- Thickness: 10 µm measured by XRF coating thickness measurement

Plating composition

Pure tin process		amts.
UTB PF-SN15	(g/L)	467
UTB PF-A	(g/L)	125
Commercial additive	(ml/L)	30
Sn2+	(g/L)	70
Free acid	(mol/L)	1.4

Tin-2%bismuth process		amts.
UTB PF-TIN15	(g/L)	533
UTB PF-BI15	(g/L)	26.7
UTB PF-ACID	(g/L)	125
UTB PF-05SH-A	(ml/L)	30
UTB PF-05SH-B	(ml/L)	10
Sn2+	(g/L)	80
Bi3+	(g/L)	4
Free acid	(g/L)	140

Plating condition

Pure tin process		
Cathodic current dencity	(A/dm2)	15
bath tempearute	()	40
Anode material		Tin

Tin-2%bismuth process					
Cathodic current d	(A/dm2)	15			
bath tempearute	()	50			
Anode material		Tin			

UNICON ISHIHARA CHEMICAL

3

2008/10/6

Ishihara Chemical co., ltd., all rights reserved.







